Eye protection - Stylish spectacles

EVASAND



>>Uses (*)

Thanks to its technical characteristics, this equipment is particularly suitable for all major works requiring protection against mechanical risks and projections including: grinding, carpentry, polishing, industry, laboratories, sports etc ... UV protection.

>>Technical features

- Style: fully adjustable safety eyewear.
- UV protection. Anti-scratch clear polycarbonate lens.
- Lens thickness: 2.00 mm.
- Sidearms: polyamide, grey colour.
- ✓ Nose bridge: P.V.C.
- Weight: 29 grams.
- Packing: carton of 100 units.
 box of 10 units.
 - each pair in individual polybag with leaflet.

More information: www.singer.fr

>> Advantages

- ✓ Wrap-around protective eyewear combining fashion, fit and function.
- Light weight, frameless design ensures a comfortable and custom fit all day long.
- Adjustable temple length enables wearers to fit the eyewear to their facial profile.
- ✓ Features with soft, slip resistant nose bridge for comfort.
- Pantoscopic adjustment allow lens angle modification.
- → The ISO9001 manufacturing ensures a perfect and constant quality.

>> Conformity

This product has been tested according to the following European Standards:

- EN 166: 2001. Personal eye-protection. Specifications.
- EN 170: 2002. Personal eye-protection. Ultraviolet filters. Transmittance requirements and recommended use.
 It complies with the European Regulation (EU) 2016/425 on Personal Protective Equipment (PPE). Category II.
 EU type examination certificate (module B) issued by BSI (Netherlands). Notified body n°2797.

Download the EU declaration of conformity on: http://docs.singer.fr

Mechanical protection	Symbol FT	Impact resistant against high speed particles at high temperatures (corresponds to the impact of a steel ball with a diameter of 6 mm and a minimum mass of 0.86 g launched at 45 m/s).
Optical quality	Symbol 1	Class 1: continuous works (better quality).
Scale number	Symbol 2C.1.2	Colour perception: not impaired Typical application: for use with sources that emit UV radiation predominantly at wavelengths < 313 nm and when glare is not an important factor. This applies to UVC and most UVB radiation ^(b) . Typical source ^(a) : Low pressure mercury vapour lamps, such as those used to stimulate fluorescent or "black lights", actinic and germicidal lamps. (a) The example given for typical source is for general guidance. (b) The wavelengths of these bands are recommended by IEC (that is UVB 280 nm to 315 nm & 100 nm to 280 nm for UVC).

Your distributor SINGER® SAFETY







(F